


SW-40・SW-50・SW-53・SW-55
 SW-N40・SW-N50・SW-N55
 SW-T40・SW-T55



型番	W	H	D	a	b	c	d	t1	t2	t3	R1	R2
SW-40・SW-N40・SW-T40	30	20	40	26	36	22.8	32.8	1.8	2	5	1.5	1
SW-50・SW-N50	35	25	50	30.2	45.2	27.8	42.8	2.3	2	5	1.5	1
SW-53	36	11	53	32	49	29.2	46.2	1.8	1.8	4.8	1.5	1.25
SW-55・SW-N55・SW-T55	40	20	55	35.5	50.5	32.8	47.8	2	2	5	1.5	0.3